




Soleko S.p.A.  
03037, Via Ravano snc  
Pontecorvo (FR) - ITALY  
info@soleko.it  
MADE IN ITALY

www.soleko-iol.it



## ASTIGMATISM CORRECTION FOR EVERYONE



# PRIME PLUS ONE

TORIC

INTRAOCULAR LENS

CIRCA IL 60% DEI PAZIENTI CHE SI SOTTOPONGONO A CHIRURGIA DELLA CATARATTA HA UN ASTIGMATISMO COMPRESO TRA 0,50 E 1,25 D.



DA UNA NOSTRA STATISTICA DI VENDITA SU 14.000 LAC TORICHE CON CILINDRO TRA 0,50 E 1,25 D, IL 70% HA UN ASSE COMPRESO TRA 70 E 110°.

DA QUI LA NOSTRA SCELTA DI POSIZIONARE L'ASSE DEL CILINDRO PLUS ONE A 90°, AL FINE DI RIDURRE LA ROTAZIONE DELLALENTE.

*APPROXIMATELY 60% OF PATIENTS HAVING SURGERY OF CATARACT HAS AN ASTYGMATISM BETWEEN 0.50 AND 1.25 D.*

*ACCORDING TO OUR SALES STATISTICS ON 14,000 TORIC CONTACT LENSES WITH CYLINDER BETWEEN 0.50 AND 1.25 D, 70% HAS AN AXIS BETWEEN 70 AND 110°.*

*THIS EXPLAINS OUR DECISION TO POSITION THE AXIS OF THE PLUS ONE*



<b>DIAMETRO OTTICO</b> <i>OPTIC DIAMETER</i>	6.0 mm
<b>DIAMETRO TOTALE</b> <i>TOTAL DIAMETER</i>	11.8 mm
<b>ANGOLAZIONE ANSA</b> <i>HAPTIC ANGULATION</i>	5°
<b>BORDO DELL' OTTICA</b> <i>EDGE DESIGN</i>	Square edge sul retro ansa e zona ottica <i>Square edge on the back loop and optical area</i>
<b>MATERIALE</b> <i>MATERIAL</i>	Acrilato pieghevole con 25% H <sub>2</sub> O e filtro UV <i>Foldable acrylic with 25% H<sub>2</sub>O and UV filter</i>
<b>INDICE DI RIFRAZIONE</b> <i>REFRACTIVE INDEX</i>	1.461 (546 nm - 20C° Hydrated)
<b>GAMMA POTERI</b> <i>DIOPTR RANGE</i>	da + 0.00 D a +10.00 D (step 1.00 D) da +10.50 D a +30.00 D (step 0.50 D)
<b>CILINDRO</b> <i>CYLINDER</i>	+ 1.00 D Ax 90°, 270°
<b>COSTANTE A CONSIGLIATA</b> <i>RECOMMENDED A CONSTANT</i>	119.3 (ultrasound biometry) 119.9 (optical biometer)
<b>COMPATIBILE CON CARTRIDGE</b> <i>RECOMMENDED CARTRIDGE</i>	2.0 - 2.1 mm